

APPLICATION NOTE

IX Series Video Door Station Streaming to exacqVision[®] Client*

The IX Series video door stations can be viewed by the exacqVision client using the RTSP connection method. By default, IX Series video door stations have the second video stream turned on and set to stream using the H.264 protocol. When configuring, verify door station settings.

exacqVision® Client Screen Setup

Configuring with ONVIF instead of RTSP may cause errors. If ONVIF method was used, cycle power to the video door station and configure using the RTSP method described below.

1 Open the exacqVision client and click Setup Setup button.

- 2 Select Add IP Cameras from the menu on the left.
- 3 Click New button under IP Camera List.

4 Enter the door information into the **IP Camera Information** section.

- Device Type: RTSP
- Hostname/IP Address: rtsp://[ip address]/udp/unicast/aiphone_H264 rtsp://[ip address]/udp/unicast/aiphone_JPEG
- Username: aiphone
- · Password: aiphone





When using the default H.264 protocol, enter the address ending in H264. For MJPEG, use the Support Tool to change the streaming method of the video door station and enter address ending in JPEG.

5	Click	Apply.	
---	-------	--------	--

V	exacqVision Client	- Ə ×
🖳 Q 🚳 🕣		🔛 🕞 exacqVision
Configuration Systems	Add IP Cameras	
	IP Camera List	Information
Wiews	Enabled Address Type A Model MAC Firmware Status	Device Type: RTSP
Tours	stsp://192.168.0.13/udp/upicast/ainhone_H264_RTSPConnected	
exacqVision Server	Hostname	/IP Address: rtsp://192.168.0.13/udp/unicast/aiphone_H264
	2	Port:
🛓 🚽 Camera Recording	4	Username: aiphone
→ Stream → Stream		Password:
Storage		
	Passv	ord Confirm:
Serial Profiles		
Event Linking 	New -3	5 Apply Cancel
Sers Users		
	Find IP Cameras Address IP Cameras	
		Show used cameras
	Select All Cameras	Q Search 🛞
	Add Reported Name Address Type 🛦 Model MAC Firmware Addressable Systems	
	AXIS%20M1054 192.168.0.90 ONVIF M1054 No	
	192.168.0.206 OW/IF No 192.168.0.20 Panasonic ST162 00-80-F0-44-91-1B No	

Tested with exacqVision[®] Client Version: 6.4.5.68890 (x86)