

Cloud Camera Quick Sizing Guide for Internal Storage

Cameras	Format	Aspect	Resolution	FPS	H.265 Stream		~ Days of in-camera storage (24x7)				
					Quality	Mbps	32GB	64GB	128GB	256GB	512GB
TCCFS08	8MP	16:9	3840 x 2160	>=15	4K	4.0	0.9	1.8	3.6	7.2	14.4
				<15	2K	2.0	1.7	3.4	6.8	13.6	27.2
	6MP	16:9	3264 x 1840	>=10	2K	2.0	1.7	3.4	6.8	13.6	27.2
				<10	HD	1.0	3.3	6.6	13.2	26.4	52.8
TCCFS03	3MP	4:3	2048 x 1536	>20	2K	2.0	1.7	3.4	6.8	13.7	27.3
				10 - 20	HD	1.0	3.3	6.6	13.2	26.4	52.8
				<10	SD	0.5	6.2	12.4	24.8	49.6	99.2
	2MP	16:9	1920 x 1080	>15	HD	1.0	3.3	6.6	13.2	26.4	52.8
				<=15	SD	0.5	6.2	12.4	24.8	49.6	99.2
	1MP	16:9	1280 x 720	>20	HD	1.0	3.3	6.6	13.2	26.4	52.8
<=20				SD	0.5	6.2	12.4	24.8	49.6	99.2	
TCCFS02	2MP	16:9	1920 x 1080	>15	HD	1.0	3.3	6.6	13.2	26.4	52.8
				<=15	SD	0.5	6.2	12.4	24.8	49.6	99.2