



# Cloudvue Gateways

Easily migrate and streamline video to the cloud



## Cloud First Design

Easy installation without the need to forward or open ports



## Scalable Deployments

Choose your version from 4-100 cameras



## Full Featured Cloud VMS

Cloud UI for live, recorded video and analytics



## iOS and Android apps

Compatible with iPhone and Android



## Multiple Storage Configurations

On board or cloud storage options



## Cyber Secure

NDAA compliant, exceeds JCI security requirements

# Specifications

|                                       | TCGD Gateway  | TCGK Gateway               | TCGT Gateway  | TCGP Gateway  | TCGS Gateway  | TCGHR Gateway   |
|---------------------------------------|---|----------------------------|---|---|---|---|
| Standard Gateways<br>Internal Storage | TCG4D1<br>(1TB)   | TCG16K1<br>(1TB)           | TCG24T4 (4TB)<br>TCG24T8 (8TB)<br>TCG24T12 (12TB)<br>TCG24T16 (16TB)<br>TCG24T24 (24TB)<br>TCG24T32 (32TB)<br>TCG24T40 (40TB) | TCG32P4 (4TB)<br>TCG32P8 (8TB)<br>TCG32P12 (12TB)<br>TCG32P16 (16TB)<br>TCG32P24 (24TB)<br>TCG32P32 (32TB)<br>TCG32P40 (40TB) | TCG40S4 (4TB)<br>TCG40S8 (8TB)<br>TCG40S12 (12TB)<br>TCG40S16 (16TB)<br>TCG40S24 (24TB)<br>TCG40S32 (32TB)<br>TCG40S40 (40TB) | TCG100R36 (36TB)<br>TCG100R72 (72TB)<br>TCG100R96 (96TB)<br>TCG100R120(120TB) |
| <b>Special Gateways</b>               | TCGVBOX02 2 cameras per box, no on-board storage, 4G cellular networks, IP66, NEMA 4X, 10"x8"x16" (HxWxD), 120VAC   |                            |   |   |   |   |
| <b>Size + Weight</b>                  |   |                            |   |   |   |   |
| Length                                | 4.72 in (120mm)   | 4.64 in (118 mm)           |   | 11.0 in (279 mm)  |   | 25.5 in (648 mm)  |
| Width                                 | 7.48 in (190mm)   | 5.82 in (148 mm)           |   | 8.27 in (210 mm)  |   | 17.2 in (437 mm)  |
| Height                                | 1.72 in (44mm)  | 1.72 in (44 mm)            |   | 9.45 in (240 mm)  |   | 3.5 in (89 mm)  |
| Weight                                | 2.65 lbs (1.2 kg)   | 2.2 lbs (1 kg)             |   | 15 lbs (6.8 kg)   |   | 72 lbs (32.6 kg)  |
| <b>Construction</b>                   |   |                            |   |   |   |   |
| Material                              | Steel, Plastic,<br>1x 40mm Fan  | Rugged Aluminum<br>Fanless |   |   |   | Steel, Plastic  |
| <b>Camera Support</b>                 |   |                            |   |   |   |   |
| Maximum Cameras                       | Up to 16  |                            | Up to 24  | Up to 32  | Up to 40  | Up to 100   |
| Manufacturers                         | Supports most cameras from leading manufacturers  |                            |   |   |   |   |
| Audio                                 | Two-way audio speaker support   |                            |   |   |   |   |
| Standard                              | ONVIF compliant   |                            |   |   |   |   |
| <b>Connections</b>                    |   |                            |   |   |   |   |
| Ethernet                              | 2 x 1GB ETH   |                            |   |   |   |   |
| <b>Operating Environment</b>          |   |                            |   |   |   |   |
| Temperature                           | 0°C to 40°C<br>(32°F to 104°)<br>RoHS Compliant   |                            |   | 0°C to 40°C<br>(32°F to 104°)   |   |   |
| Web Browser Interface                 | Responsive design / No plugins / Common browser support   |                            |   |   |   |   |
| Mobile App Interface                  | iOS, Android native apps  |                            |   |   |   |   |
| Setup                                 | Plug + play Installation, auto camera configuration   |                            |   |   |   |   |
| Hyper View                            | View 24 hours in 60 seconds   |                            |   |   |   |   |
| Motion View                           | Live video view from motion detecting cameras only  |                            |   |   |   |   |
| Cloud Drive                           | On-demand cloud storage, record on motion or schedule, save bookmarks or clips  |                            |   |   |   |   |
| Site View                             | Floor plan camera maps, drag and drop interface, live camera views  |                            |   |   |   |   |
| User Management                       | Unlimited users, custom permissions, local/remote management, custom camera views per user  |                            |   |   |   |   |
| System Management                     | Enterprise status dashboard, remote troubleshooting, process RAM/HDD/memory status, health check/check speed, bandwidth utilization, user/subscription management |                            |   |   |   |   |
| Scheduling                            | Day/time/camera/custom recording  |                            |   |   |   |   |
| Live Video                            | Fast global live video, custom layouts/views, full screen playback, digital PTZ, optical PTZ/presets, multiple location views                                     |                            |   |   |   |   |
| Recorded Video                        | Timeline search with preview, event search with preview, Hyper View search, full screen playback, search date and time, bookmark/comment save clips               |                            |   |   |   |   |
| <b>Analytics / Intelligence</b>       |   |                            |   |   |   |   |
| All Cameras                           | Motion, People, Vehicle, Heat Map   |                            |   |   |   |   |
| Illustra Pro Cameras                  | People count, object detect/remove, linger, dwell, enter/exit, crowd, queue   |                            |   |   |   |   |
| API                                   | Open RESTful API  |                            |   |   |   |   |
| Language Support                      | English, French, Italian, German, Spanish, Russian, Portuguese  |                            |   |   |   |   |



TCG16K  
16 Cameras, 1-2TB



TCG24T  
24 Cameras, 4-40TB



TCG32P  
32 Cameras, 4-40TB



TCG40S  
40 Cameras, 4-40TB



TCG100R  
100 Cameras, 36-120TB

CV1392-DS-202301-R02-HS-EN