

Does exacqVision Work with Nested Active Directory Groups?

Yes with server version 6.8 and later.

The admin needs to select Active Directory (Nested) as the schema in the AD/LDAP configuration screen.

The screenshot shows the 'Configure System' interface with the 'ActiveDirectory/LDAP' tab selected. The 'Directory Service' section is expanded, showing a status of 'Connected' and 'Enable Directory Service' checked. The 'LDAP Server Address' section includes a text box for 'Hostname/IP Address' containing 'cfsad.com', a 'Port' field with '636', and a checked 'Use SSL' checkbox. Below this, there is a 'Permission to Create SPN' checkbox (unchecked) and an 'SPN' field containing 'HOST/EVACTIDEMO.cfsad.com'. The 'LDAP Schema' dropdown menu is highlighted with a red box and currently displays 'Active Directory (Nested)'. Other fields include 'LDAP Base DN', 'LDAP Binding DN', 'LDAP Password', and 'Confirm' (all masked with dots). The 'Enable Local User Accounts' checkbox is also checked. The 'Search Settings' section includes 'Search Item Limit' (100), 'Search Timeout' (5 Seconds), 'Follow Referrals' (unchecked), and 'Active Directory User Disabling' (checked). At the bottom, there are buttons for 'Query AD/LDAP', 'Apply', and 'Cancel'.