

To determine the make and model of the motherboard installed in an exacqVision system, complete the following steps:

1. Click Start, type **cmd**, and press Enter to open a Command Prompt.
2. Type **systeminfo** and press Enter to display information about the motherboard.

```

C:\Windows\system32\cmd.exe
Microsoft Windows [Version 6.1.7601]
Copyright (c) 2009 Microsoft Corporation. All rights reserved.






C:\Users\rakesh.sharma>systeminfo

Host Name:                RAKESHSHARMA-PC
OS Name:                  Microsoft Windows 7 Professional
OS Version:              6.1.7601 Service Pack 1 Build 7601
OS Manufacturer:        Microsoft Corporation
OS Configuration:       Member Workstation
OS Build Type:            Multiprocessor Free
Registered Owner:        x
Registered Organization:
Product ID:               00371-OEM-8992671-00524
Original Install Date:    8/16/2012, 9:51:11 AM
System Boot Time:         9/27/2012, 5:23:11 PM
System Manufacturer:      Dell Inc.
System Model:              Precision M6600
System Type:               x64-based PC
Processor(s):              1 Processor(s) Installed.
                           [01]: Intel64 Family 6 Model 42 Stepping 7 GenuineInt
                           el ~2401 Mhz
BIOS Version:              Dell Inc. 010, 5/13/2012
Windows Directory:        C:\Windows
System Directory:         C:\Windows\system32
Boot Device:               \Device\HarddiskVolume2
System Locale:              en-us;English (United States)
Input Locale:              en-us;English (United States)
Time Zone:                 (UTC-05:00) Eastern Time (US & Canada)
Total Physical Memory:     8,074 MB
Available Physical Memory: 5,123 MB
Virtual Memory: Max Size:  16,147 MB
Virtual Memory: Available: 12,732 MB
Virtual Memory: In Use:    3,415 MB
Page File Location(s):    C:\pagefile.sys
Domain:                    exacq.org
Logon Server:              \\EXACQSERVER2008
Hotfix(s):                  107 Hotfix(s) Installed.
                           [01]: KB971033
                           [02]: KB2425227
                           [03]: KB2479943
                           [04]: KB2484033
                           [05]: KB2488113
                           [06]: KB2491683
                           [07]: KB2492386
                           [08]: KB2505438
                           [09]: KB2506014
                           [10]: KB2506212
    
```


3. Find the **System Manufacturer** and **System Model** entries. (In the preceding example, the motherboard is a Precision M6600 from Dell Inc.)

NOTE: If necessary, maximize the window or scroll up to display the full list.


4. Alternatively, look at the back of the system and match the connector layout to the following images:







*Only 2 Video outputs at a time 1 from either DVI-I or DVI-D and the display port



Super Micro - C7Q67 A and Z Series
 A = i3 Standard, i5 Option
 Z = i7 Standard





*Only 2 of 3 Video outputs available
 Both HDMI or 1 HDMI and 1 VGA



*Only 2 Video outputs at a time 1 from either DVI-I or DVI-D and the display port

Super Micro - X7SPA Atom EL Series
 Dual NIC Option for the Mini



BCM - RX67Q DT Only



*Only 2 of 3 Video outputs available
 HDMI, VGA or DVI-D

J.P. 8/8/12 - Rev # 2