





Tyco Illustra Pro 5MP Thermal EST Camera Elevated Skin Temperature Scanning Solution with Tyco Cloudvue Integration



Key Features

- Dual Image Sensor with thermal detector
- Up to 5MP resolution 2592 x 1944 with visible camera, 384 x 288 resolution with thermal camera
- True day / night
- Built in IR and white light illuminator
- True WDR, up to 120dB
- Smart facial temperature detection
- Alarm trigger by temperature anomaly
- High accuracy with blackbody calibration to $\pm 0.2^{\circ}\text{C}$ ($\pm 0.4^{\circ}\text{F}$) in Single Face usage mode
- Customizable sound-light alarm
- 1-CH audio input; 1-CH built-in speaker
- PoE or 12VDC powered
- IP66 rating for outdoor application
- NDAA Compliant

What is the Smart Temperature Scanning Solution?

Johnson Controls smart elevated skin temperature scanning solution comprises of a dual sensor, one Thermal the other Color, camera and a temperature calibration device known as a Blackbody. Using advanced face detection technology and in conjunction with the dual sensors, the camera will measure the temperature of a person's forehead whilst the blackbody provides the constant temperature reference point. Should someone in the field of view be detected with a skin temperature above a predetermined level, an operator can be alerted to this fact through a variety of possible methods ranging from alerts in the VMS, events in a Access Control system, via a connected light/sounder to the camera, or even through a web browser connection.

Cloud Integration

Seamless integration with Tyco Cloudvue enables instant SMS and e-mail alerts when elevated skin temperature is detected. Tyco Cloudvue enables remote management and stores elevated skin temperature alerts online for reporting and auditing purposes.

The International Electrotechnical Commission (IEC) standards for the basic safety and essential performance of screening thermographs for human febrile temperature screening are at the heart of the development of the Johnson Controls smart elevated skin temperature scanning solution, tested by UL for accuracy, drift, stability and uniformity of the IEC 80601-2-59:2017 standard. High accuracy brings with it the benefit of reducing false alarms to a minimum, which in turn results in fewer disruptions and increased flow of staff and visitors.

Contactless and Accurate

Complying with the U.S. Food & Drug Administration's COVID-19 Enforcement Policy criteria released in April 2020, the The Tyco Illustra Pro Thermal EST Camera, being contactless and therefore non-invasive, is ideal for deployment at controlled entrances to areas and facilities where initial skin temperature measurement is needed for staff and visitors. With $\pm 0.2^{\circ}\text{C}$ ($\pm 0.4^{\circ}\text{F}$) accuracy tolerance at an effective distance of 1~2 meters (3.3~6.6 feet), this elevated skin temperature scanning solution provides a high degree of flexibility to meet the individual situational awareness requirements of a wide variety of installations.


Specifications

Dual imager camera	
Thermal camera	
Detector type	Amorphous-silicon Bolometers
Pixel pitch	17 μm
Infrared spectral range	8~14 μm
Effective pixels	384 × 288
Noise equivalent temperature difference	<35mK
Thermal response time	≈40ms
Lens type	Fixed
Focal length	12mm @ F1.0
Field of view	Horizontal 29.7°, Vertical 22.5°
Visible camera	
Imager	1 / 2.7" 5MP Progressive CMOS
Effective pixels	2592 x 1944
Minimum illumination	Color 0.012 Lux @ F2.0 B/W 0.0012 Lux @ F2.0, 0 Lux with IR
Shutter speed	1/30 s ~ 1 / 10,0000 s
S/N ratio	≥52 dB
Lens type	Fixed
Focal length	8mm
Field of view	Horizontal 38°, Vertical 27.5°
Lens mount	M12
Video	
Video compression	H.264 / H.265 / MJPEG
H.264 Compression standard	Base Line / Main Profile / High Profile
H.265 Compression standard	Main Profile @ Level 4.1 High Tier
Resolution	Visible 5MP (2592x1944), 4MP (2592x1520), 2560x1440, 3MP (2304x1296), 1080P (1920x1080), 720P (1280x720), D1 (720x576), 480x240, CIF (352x240) Thermal 704x576 (Upscaled from 384x288)
Maximum frame rate	Visible: 30 fps @ all resolution. Thermal: 30 fps @ 704x576 (Upscaled)

Video bit rate	64 Kbps ~ 5 Mbps
Multiple streaming	Triple stream
Main stream	Visible 2592x1944, 2592x1520, 2304x1296, 1920x1080, 1280x720
	Thermal 704x576 (Upscaled from 384x288)
Second stream	Visible 1280x720, 704x480, 352x240
Third stream	Visible 704x576, 480x240, 352x288
Bitrate control	VBR / CBR
Quality control	5 levels under VBR; Freely adjustable under CBR
Image setting	ROI, Saturation, Brightness, Chroma, Contrast, Wide Dynamic, Sharpen, NR
Audio	
Audio communication	1-CH audio input; 1-CH built-in speaker
Audio compression format	G .711A, G.711U
Audio bit rate	128 Kbps
Operational	
Day and night	True Day/Night with Auto IR Cut Filter
Backlight compensation	BLC/HLC
Wide dynamic range	True WDR, 120dB
Effective ir distance	20 metres (65.6 feet)
Digital noise reduction	2D/3D DNR
Digital zoom	Yes
Video privacy	4 zones video mask
Smart codec	8 zones ROI
Display mode	Visible only, Picture-in-picture, Dual Window
Intelligent video analytics	Visible Camera Line crossing direction, Object Abandoned / Removed, Enter an area, Motion detection
	Thermal Camera Elevated Skin Temperature Detection
Alarm triggers	Alarm in, Intelligent video analytics, Network disconnect, SD card full, SD card error
Backfilling	iAPI3
Temperature detection	
Detection mode	Multiple point forehead skin temperature detection
Detection preset	Single Face (in accordance with IEC standards) *
Effective distance	1~2M (3.3 ~ 6.6 feet) in Single Face usage mode
Temperature alarm	Over temperature / Temperature anomaly
Response time	Less than 50ms
Calibration	Automatic calibration with blackbody
Accuracy	±0.2°C (±0.4°F) in Single Face usage mode with blackbody calibration
Network	
Network protocol	TCP / IP, UDP, DHCP, NTP, RTSP, PPPoE, DDNS, SMTP, FTP, SNMP, UPnP, Unicast, Multicast
Cyber security	HTTPS / IP Filter / IEEE 802.1X / Firewall / account security
Online connection	Support simultaneous monitoring for up to 10 users
API	ONVIF, iAPI3

Interface	
Network	RJ45
Audio	1-CH audio input; 1-CH built-in speaker
Alarm	Alarm in/out, Built-in sound-light alarm, Customizable voice alarm
Hardware reset	Supported
Environmental	
Operating temperature	0°C ~ 35°C (32°F ~ 95°F)
Operating humidity	10% ~ 90% relative humidity
Ingress protection	IP66
General	
Power supply	DC12V / PoE
Power consumption	<9W
Dimensions (LxWxH)	10.94 inches (278mm) x 3.78 inches (96mm) x 3.50 inches (89mm)
Net weight	2.6lbs, 1.2Kg
Installation	Wall mounting, Ceiling mounting, Tripod mounting
Certification	Certification testing is pending for major markets, including North America and the European Union.

Dimensions



Blackbody Calibrator

Temperature range	20.0°C to 70.0°C (68°F to 158°F)
Emissive area	100mm x 100mm
Display resolution	0.01°C (0.0018°F)
Radiance temperature expanded uncertainty	± 0.25°C between 33°C and 40°C (± 0.45°F between 91.4°F and 104°F)
Stability	± 0.05°C (± 0.09°F)
Emissivity ratio	0.96
Power supply	120 - 240 VAC compatible 50/60 Hz
Net weight	2kg (4.4lbs)
Calibration certificate	24 months from manufacturing

Ordering Information

Model	Description
IPT05-B29-BNDA3	Dual imager temperature detection camera, Visible/Thermal, 5MP/384*288, 8mm/12mm, 20M IR, sound-light alarm, Alarm/Audio, Micro SD, DC/PoE, IP66, 110V Blackbody calibration device included

Accessories

Model	Description
IATR-ISTR	Tyco Illustra Pro Thermal EST Camera or Black Body Tripod Mount - 1/4"-20
IBJB-TIS-WB-A	Tyco Illustra Pro Thermal EST Back Box Mount
IBJB-TIS-WB-B	Tyco Illustra Pro Thermal EST Back Box With Side Conduit Opening
IBPN-TIS-WB	Tyco Illustra Pro Thermal EST Ceiling Pendant Mount (Requires a Back Box IBJB-TIS-WB-A or IBJB-TIS-WB-B)
IBPM-TIS-0	Tyco Illustra Pro Thermal EST Pole Mounting Box with Straps (Requires a Back Box IBJB-TIS-WB-A or IBJB-TIS-WB-B)
IBCM-TIS-0	Tyco Illustra Pro Thermal EST Corner Mount (Requires a Back Box IBJB-TIS-WB-A or IBJB-TIS-WB-B)

Important Notice: Elevated body temperatures identified by the Tyco Illustra Pro Thermal EST should be confirmed with secondary evaluation methods, such as contact thermometers. Temperature measurements should not be solely or primarily relied upon to diagnose or exclude a diagnosis of COVID-19, or any other disease. The Tyco Illustra Pro Thermal EST does not cause and cannot eliminate or prevent occurrences of the events that it is intended to detect or avert. This product is not intended to diagnose or monitor any medical condition or illness and should not be used as such. The product is supplied as a first-line filter for organisations that wish to identify those entering premises who may have an elevated body temperature. It is then for the organisation to determine how that information is used, and the appropriate reaction to that information. Competent medical advice should be sought if there are concerns around illness, and further checks will be required.

About Johnson Controls

Johnson Controls is a global diversified technology and multi-industrial leader serving a wide range of customers in more than 150 countries. Our 120,000 employees create intelligent buildings, efficient energy solutions, integrated infrastructure and next generation transportation systems that work seamlessly together to deliver on the promise of smart cities and communities. Our commitment to sustainability dates back to our roots in 1885, with the invention of the first electric room thermostat.

For additional information, please visit www.illustracameras.com or follow Illustra on LinkedIn, Twitter, and Facebook.